**Defender 500 Series** 

**Defender 510** Volumetric Primary Flow Standard

**Defender 520** Enhanced Volumetric Primary Flow Standard

## **Defender 530**

Standardized and Volumetric Primary Flow Standard

## **Bios Defender 500 Series**



Turn the Defender on. Connect it to your pump. Take measurements. It's that simple. Instantly calibrate your gas flow using Quick Start – there is no preparation involved, no messy soap bubble solutions. Defender's many user-selectable options makes customizing your calibrations easy, giving you exactly what you need in the format you prefer. All you have to do is choose between the 510, the 520 or the 530.

		Defender 510	Defender 520	Defender 530
Model and Flow Ranges		510L, 5-500 ccm 510M, 50-5000 ccm 510H, 300-30,000 ccm	520L, 5-500 ccm 520M, 50-5000 ccm 520H, 300-30,000 ccm	530L, 5-500 ccm 530M, 50-5000 ccm 530H, 300-30,000 ccm
Volumetric Accuracy		1%	1%	1%
Standardized Accuracy		N/A	N/A	1.2%
User selectable Measurement Units	Volumetric	mL/min, L/min, cc/min, cf/min	mL/min, L/min, cc/min, cf/min	mL/min, L/min, cc/min, cf/min
	Standardized	N/A	N/A	smL/min, sL/min, scc/min, scf/min
	Temperature	N/A	°C °F	°C °F
	Pressure	N/A	mmHg, PSI, kPa	mmHg, PSI, kPa
Temperature and Pressure Sensor		No	Yes, in flow stream	Yes, in flow stream
Pressure Accuracy		N/A	± 3.5 mmHg (typical) ± 7.0 mm (max)	$\pm$ 3.5 mmHg (typical) $\pm$ 7.0 mm (max)
Temperature Accuracy		N/A	± 0.8° C (typical) ± 1.3° C (max)	± 0.8° C (typical) ± 1.3° C (max)



8]ghf]VihYX'6m<sup>.</sup> 5]f!AYhGVJYbhjZJWDhmi@tX<sup>.</sup> Úkárì€∈∕€€€€ÂIIIÁ Økár쀀∕€€€€ÂIIIÁ Ôkáca¢^•Oæa{^d&[{ Èĕ ÁÂ Y ká,, Èæá{^d&[{ Èĕ Á

Defender 500 Series			
Approximate Time per reading	1-15 seconds		
<b>Reading Styles</b> (with averaging function user-selectable from 1 to 100 measurements)	Single (manual), Continuous or Burst		
Gas Compatibility	non-corrosive gases, non-condensing, less then 70% humidity		
Flow Modes	Pressure or Suction		
Measurement Cell Style	Integrated		
AC Adapter/Charger	12V DC, > 250ma, 2.5mm center positive		
Battery System	6v rechargeable, sealed lead-acid, 6-8 hrs typical operation		
<b>Battery Operational Time</b> (5 cycles/min)	3 hours backlight on, 8 hours backlight off		
Pressure and Suction Fittings	¼" ID Hose Barb		
Warranty	1 yr (battery 6 mo)		
Storage Temperature	0-70° C		
Ambient Humidity	0-70%, non-condensing		
<b>Operating Pressure</b> (Absolute)	Atmospheric, Maximum 15 PSIA		
Display	backlit graphical LCD		
Data Port (for PC intereface)	Serial - RS-232		
Data Cable (for PC intereface)	1 meter Defender to PC included		
Protective Case	Pelican case available		
Dimensions (H x W x D)	5.5" x 6" x 3" / 140 x 150 x 75 mm		
Weight	29 oz / 820 g		
RoHS- and CE-compliant			





Mesa's Butler, N.J. manufacturing facility (pictured above) is our NVLAP accredited ISO 17025 laboratory.

